





DRM-A

DRM-D

Ordering Information



Tech-Quality Co.,Ltd.



Call: +662-3286878



2/13 Sukapiban 2 Rd., Pravet,Pravet, Bangkok 10250 Thailand






www.tech-quality.com



info@tech-quality.com





Durometer Test Stand

DRM The DRM Series Operating Stand is the ideal tool for repetitive or lab-type testing for users who must test either large specimens, or test in a number of different durometer scales.

The DRM Operating Stand, used in conjunction with a durometer eliminates the operator error sometimes associated with shop floor durometer testing.

The stand features a floating pin and includes the proper load weights required for testing in durometer scales, Each durometer of type A,E,B,O and SRIS with fixing around 1 kg weight and type D,DO,C with fix around 5 kg, as noted in ASTM D2240, ISO,JIS





DRM-A


Specification

DRM-A with fixing around 1 kg weight DRM-D with fixing around 5 kg weight Adjusted glass stage

These equipment can help us test the hardness more acutely



Durometer Test Stand







Option Weight (4kg) for 5kg

Features

Used in the durometer of type A, type B or type O, type OO directly.

Dimension





Specification

Operating Type: Indentor to specimen

Loading Method: Cam loading

Loading Stroke: 18 mm

Specimen Thickness: 60 mm

Throat Depth: 65 mm

Support Table (dia.): 116 mm

Lifting Adjustment : Screw adjustment

Table Adjustment : Three-point leveling

Net Weight: 5.6kg(excluding S weight)

Package Weight: 7.6kg(excluding D weight)